

PRECISION FX-iWP Series Washdown

Standard Features

- Washdown IP65 rating
- Compact Super Hybrid Sensor Technology (SHS)
- Vacuum Fluorescent Display (VFD)
- GLP/GMP/ISO compliant to either AD-8121 printer or computer. Transmits date, time, ID number, serial number and calibration data
- RS-232 interface for connecting to printer or PC
- Response indicator function
- Underhook weighing

Specifications

Weighing Units

Pound, Carat, Pennyweight, Troy Ounce, Grain, Pound/Ounce

Operating Modes

Weigh, Count, Percent, Animal Weighing, Statistical, Hold and Comparator

Power

120/240 VAC adapter, approx. 11 VA

Stabilization Time

Approx. 1 second

Sensitivity Drift (10° C to 30° C)

±2 ppm/° C

Display Refresh Rate

5 times/second, 10 times/second or 20 times/second

Calibration Weight

FX-120iWP: 100 g
FX-200iWP: 200 g
FX-300iWP: 300g

Operating Temperature

41° F to 104° F (5° C to 40° C) 85% RH or less (no condensation)

Est. Weight

8 lb (3.5 kg)

Warranty

Five-year limited warranty

Return Policy

A&D Weighing Standard Policy - restock fee may apply

Model	Capacity	Readability	Repeatability	Linearity	Pan Size	Dimensions	Part #	List Price
FX-120iWP	122 g	0.001 g	0.001 g	±0.002 g	Ø 5.12 in (130 mm)	6 x 10.3 x 3.3 in (193 x 263 x 85 mm)	102905	Consult
FX-200iWP	220 g	0.001 g	0.001 g	±0.002 g	Ø 5.12 in (130 mm)	6 x 10.3 x 3.3 in (193 x 263 x 85 mm)	102906	Consult
FX-300iWP	320 g	0.001 g	0.001 g	±0.002 g	Ø 5.12 in (130 mm)	6 x 10.3 x 3.3 in (193 x 263 x 85 mm)	102907	Consult

Options/Accessories

Part #	A&D Model #	Description	Price
98027*	FXi-02	Quick USB interface	Consult
98028*	FXi-08	Ethernet interface with WinCT [®] Plus software	Consult
98029*	FXi-09	Built-in rechargeable battery	Consult
98030	FXi-10	Small breeze break	Consult
98031	FXi-11	Large breeze break	Consult
97649	TB:648	AC adapter (120 V/220 V)	Consult

*Options FXi-02/FXi-08 and FXi-09 cannot be combined and are factory installed only.

